

Specifications

Photo is representative

Eaton QBGFT2020

Eaton QB GFCI circuit breaker, Ground fault circuit breaker, 20A, 10 kAIC, Two-pole, 120/240V, Common trip, 5 mA Trip sensitivity, #14-10 Cu, #12-10 Al, QBGF

Physical Attributes

CIRCUIT BREAKER TYPE	QBGF
MOUNTING METHOD	Bolt-on
NUMBER OF POLES	Two-pole
TYPE	Ground fault circuit breaker
WIRE SIZE	#14-10 AWG Cu #12-10 AWG Al

General specifications

PRODUCT NAME	Eaton QB GFCI circuit breaker
CATALOG NUMBER	QBGFT2020
UPC	786676026710
PRODUCT LENGTH/DEPTH	4.5 in
PRODUCT HEIGHT	2 in
PRODUCT WIDTH	2.75 in
PRODUCT WEIGHT	0.6 lb
WARRANTY	1 year
CERTIFICATIONS	UL 489
CATALOG NOTES	HACR rated



Specifications

Photo is representative

Eaton QBGFT2020

Eaton QB GFCI circuit breaker, Ground fault circuit breaker, 20A, 10 kAIC, Two-pole, 120/240V, Common trip, 5 mA Trip sensitivity, #14-10 Cu, #12-10 Al, QBGF

Physical Attributes

CIRCUIT BREAKER TYPE	QBGF
MOUNTING METHOD	Bolt-on
NUMBER OF POLES	Two-pole
TYPE	Ground fault circuit breaker

General specifications

PRODUCT NAME	Eaton QB GFCI circuit breaker
---------------------	-------------------------------

WIRE SIZE	#14-10 AWG Cu #12-10 AWG Al
------------------	--------------------------------

CATALOG NUMBER	QBGFT2020
-----------------------	-----------

UPC	786676026710
------------	--------------

PRODUCT LENGTH/DEPTH	4.5 in
-----------------------------	--------

PRODUCT HEIGHT	2 in
-----------------------	------

PRODUCT WIDTH	2.75 in
----------------------	---------

PRODUCT WEIGHT	0.6 lb
-----------------------	--------

WARRANTY	1 year
-----------------	--------

CERTIFICATIONS	UL 489
-----------------------	--------

CATALOG NOTES	HACR rated
----------------------	------------



Powering Business Worldwide