

# Specifications

Photo is representative

## Eaton QBGFT2050

Eaton QB GFCI circuit breaker, Ground fault circuit breaker, 50A, 10 kAIC, Two-pole, 120/240V, Common trip, 5 mA Trip sensitivity, #8-6 Cu, #6-4 Al, QBGF

### Physical Attributes

<b>CIRCUIT BREAKER TYPE</b>	QBGF
<b>MOUNTING METHOD</b>	Bolt-on
<b>NUMBER OF POLES</b>	Two-pole
<b>TYPE</b>	Ground fault circuit breaker
<b>WIRE SIZE</b>	#6-4 Al #8-6 Cu

### General specifications

<b>PRODUCT NAME</b>	Eaton QB GFCI circuit breaker
<b>CATALOG NUMBER</b>	QBGFT2050
<b>UPC</b>	786676026697
<b>PRODUCT LENGTH/DEPTH</b>	6.5 in
<b>PRODUCT HEIGHT</b>	2 in
<b>PRODUCT WIDTH</b>	3.5 in
<b>PRODUCT WEIGHT</b>	0.8 lb
<b>WARRANTY</b>	1 year
<b>CERTIFICATIONS</b>	UL 489
<b>CATALOG NOTES</b>	HACR rated



Powering Business Worldwide

# Specifications

Photo is representative

## Eaton QBGFT2050

Eaton QB GFCI circuit breaker, Ground fault circuit breaker, 50A, 10 kAIC, Two-pole, 120/240V, Common trip, 5 mA Trip sensitivity, #8-6 Cu, #6-4 Al, QBGF

### Physical Attributes

<b>CIRCUIT BREAKER TYPE</b>	QBGF
<b>MOUNTING METHOD</b>	Bolt-on
<b>NUMBER OF POLES</b>	Two-pole
<b>TYPE</b>	Ground fault circuit breaker
<b>WIRE SIZE</b>	#6-4 Al #8-6 Cu

### General specifications

<b>PRODUCT NAME</b>	Eaton QB GFCI circuit breaker
<b>CATALOG NUMBER</b>	QBGFT2050
<b>UPC</b>	786676026697
<b>PRODUCT LENGTH/DEPTH</b>	6.5 in
<b>PRODUCT HEIGHT</b>	2 in
<b>PRODUCT WIDTH</b>	3.5 in
<b>PRODUCT WEIGHT</b>	0.8 lb
<b>WARRANTY</b>	1 year
<b>CERTIFICATIONS</b>	UL 489
<b>CATALOG NOTES</b>	HACR rated



Powering Business Worldwide