

# Eaton QBGFT2050

Catalog Number: QBGFT2050

Eaton QB GFCI circuit breaker, Ground fault circuit breaker, 50A, 10 kAIC, Two-pole, 120/240V, Common trip, 5 mA Trip sensitivity, #8-6 Cu, #6-4 Al, QBGF

## General specifications



Photo is representative

<b>Product Name</b>	<b>Catalog Number</b>
Eaton QB GFCI circuit breaker	QBGFT2050
<b>UPC</b>	<b>Product Length/Depth</b>
786676026697	6.5 in
<b>Product Height</b>	<b>Product Width</b>
2 in	3.5 in
<b>Product Weight</b>	<b>Warranty</b>
0.8 lb	1 year
<b>Certifications</b>	<b>Catalog Notes</b>
UL 489	HACR rated

## Physical Attributes

### Circuit breaker type

QBGF

### Mounting Method

Bolt-on

### Number of poles

Two-pole

### Type

Ground fault circuit breaker

### Wire size

#6–4 Al

#8–6 Cu

## Performance Ratings

### Amperage Rating

50 A

### Interrupt rating

10 kAIC

### Trip Type

Common trip

### Trip rating

5 mA trip sensitivity

### Voltage rating

120/240 V

## Miscellaneous

### Special features

5 mA Trip Sensitivity

## Resources

### Specifications and datasheets

[Eaton Specification Sheet - QBGFT2050](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)