

# Specifications



## Eaton QBHGFT1020

Eaton QB GFCI circuit breaker, Ground fault circuit breaker, 20A, 22 kAIC, Single-pole, 120/240V, Non-Interchangeable, 5 mA Trip Sensitivity, QBHGF

### Physical Attributes

<b>CIRCUIT BREAKER TYPE</b>	QBHGF
<b>MOUNTING METHOD</b>	Bolt-on
<b>NUMBER OF POLES</b>	Single-pole
<b>TYPE</b>	Ground fault circuit breaker

### General specifications

<b>PRODUCT NAME</b>	Eaton QB GFCI circuit breaker
<b>CATALOG NUMBER</b>	QBHGFT1020
<b>UPC</b>	786680131035
<b>PRODUCT LENGTH/DEPTH</b>	5 in
<b>PRODUCT HEIGHT</b>	1 in
<b>PRODUCT WIDTH</b>	3 in
<b>PRODUCT WEIGHT</b>	0.4 lb
<b>WARRANTY</b>	1 year
<b>CERTIFICATIONS</b>	UL 489



Powering Business Worldwide

# Specifications



## Eaton QBHGFT1020

Eaton QB GFCI circuit breaker, Ground fault circuit breaker, 20A, 22 kAIC, Single-pole, 120/240V, Non-Interchangeable, 5 mA Trip Sensitivity, QBHGF

### Physical Attributes

<b>CIRCUIT BREAKER TYPE</b>	QBHGF
<b>MOUNTING METHOD</b>	Bolt-on
<b>NUMBER OF POLES</b>	Single-pole
<b>TYPE</b>	Ground fault circuit breaker

### General specifications

<b>PRODUCT NAME</b>	Eaton QB GFCI circuit breaker
<b>CATALOG NUMBER</b>	QBHGFT1020
<b>UPC</b>	786680131035
<b>PRODUCT LENGTH/DEPTH</b>	5 in
<b>PRODUCT HEIGHT</b>	1 in
<b>PRODUCT WIDTH</b>	3 in
<b>PRODUCT WEIGHT</b>	0.4 lb
<b>WARRANTY</b>	1 year
<b>CERTIFICATIONS</b>	UL 489



Powering Business Worldwide