

Specifications



Eaton QBHGFT1020

Eaton QB GFCI circuit breaker, Ground fault circuit breaker, 20A, 22 kAIC, Single-pole, 120/240V, Non-Interchangeable, 5 mA Trip Sensitivity, QBHGF

Physical Attributes

CIRCUIT BREAKER TYPE	QBHGF
MOUNTING METHOD	Bolt-on
NUMBER OF POLES	Single-pole
TYPE	Ground fault circuit breaker

General specifications

PRODUCT NAME	Eaton QB GFCI circuit breaker
CATALOG NUMBER	QBHGFT1020
UPC	786680131035
PRODUCT LENGTH/DEPTH	5 in
PRODUCT HEIGHT	1 in
PRODUCT WIDTH	3 in
PRODUCT WEIGHT	0.4 lb
WARRANTY	1 year
CERTIFICATIONS	UL 489



Powering Business Worldwide