

Specifications

Photo is representative



Eaton QBHGFT2020

Eaton QB GFCI circuit breaker, Ground fault circuit breaker, 20A, 22 kAIC, Two-pole, 120/240V, QBHGF

Physical Attributes

CIRCUIT BREAKER TYPE	QBHGF
NUMBER OF POLES	Two-pole
TYPE	Ground fault circuit breaker

General specifications

PRODUCT NAME	Eaton QB GFCI circuit breaker
CATALOG NUMBER	QBHGFT2020
UPC	786676027823
PRODUCT LENGTH/DEPTH	4.5 in
PRODUCT HEIGHT	2 in
PRODUCT WIDTH	2.75 in
PRODUCT WEIGHT	0.6 lb
CERTIFICATIONS	UL 489
CATALOG NOTES	HACR rated



Powering Business Worldwide

Specifications

Photo is representative



Eaton QBHGFT2020

Eaton QB GFCI circuit breaker, Ground fault circuit breaker, 20A, 22 kAIC, Two-pole, 120/240V, QBHGF

Physical Attributes

CIRCUIT BREAKER TYPE	QBHGF
NUMBER OF POLES	Two-pole
TYPE	Ground fault circuit breaker

General specifications

PRODUCT NAME	Eaton QB GFCI circuit breaker
CATALOG NUMBER	QBHGFT2020
UPC	786676027823
PRODUCT LENGTH/DEPTH	4.5 in
PRODUCT HEIGHT	2 in
PRODUCT WIDTH	2.75 in
PRODUCT WEIGHT	0.6 lb
CERTIFICATIONS	UL 489
CATALOG NOTES	HACR rated

Powering Business Worldwide