

# Eaton QBHW1015

Catalog Number: QBHW1015

Eaton QB thermal magnetic circuit breaker, Quicklag industrial thermal-magnetic circuit breaker, 20 A, 22 kAIC, Single-pole, 120/240 V, Non-Interchangeable, Q17, QBHW



## General specifications

|   |                       |
|---|-----------------------|
| <b>Product Name</b>                       | <b>Catalog Number</b> |
| Eaton QB thermal magnetic circuit breaker | QBHW1015              |
|   | UPC                   |
|   | 786679392003          |
| <b>Product Length/Depth</b>               | <b>Product Height</b> |
| 3.9 in                                    | 4.8 in                |
| <b>Product Width</b>                      | <b>Product Weight</b> |
| 1.2 in                                    | 0.3 lb                |
| <b>Warranty</b>                           | <b>Certifications</b> |
| 1 year                                    | UL Listed             |
|   | CSA Certified         |

## Catalog Notes

Switching duty rated for 120V fluorescent light applications, HACR rated

## Physical Attributes

### Circuit breaker type

QBHW

### Mounting Method

Bolt-on

### Number of poles

Single-pole

### Type

Quicklag industrial thermal-magnetic circuit breaker

## Performance Ratings

### Amperage Rating

15 A

### Interrupt rating

22 kAIC

### Trip Type

Non-Interchangeable

### Voltage rating

120/240 V

## Miscellaneous

### Quantity

17

## Resources

### Specifications and datasheets

[Eaton Specification Sheet - QBHW1015](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

# Eaton QBHW1015

Catalog Number: QBHW1015

Eaton QB thermal magnetic circuit breaker, Quicklag industrial thermal-magnetic circuit breaker, 20 A, 22 kAIC, Single-pole, 120/240 V, Non-Interchangeable, Q17, QBHW



## General specifications

|   |                       |
|---|-----------------------|
| <b>Product Name</b>                       | <b>Catalog Number</b> |
| Eaton QB thermal magnetic circuit breaker | QBHW1015              |
|   | UPC                   |
|   | 786679392003          |
| <b>Product Length/Depth</b>               | <b>Product Height</b> |
| 3.9 in                                    | 4.8 in                |
| <b>Product Width</b>                      | <b>Product Weight</b> |
| 1.2 in                                    | 0.3 lb                |
| <b>Warranty</b>                           | <b>Certifications</b> |
| 1 year                                    | UL Listed             |
|   | CSA Certified         |

## Catalog Notes

Switching duty rated for 120V fluorescent light applications, HACR rated

## Physical Attributes

### Circuit breaker type

QBHW

### Mounting Method

Bolt-on

### Number of poles

Single-pole

### Type

Quicklag industrial thermal-magnetic circuit breaker

## Performance Ratings

### Amperage Rating

15 A

### Interrupt rating

22 kAIC

### Trip Type

Non-Interchangeable

### Voltage rating

120/240 V

## Miscellaneous

### Quantity

17

## Resources

### Specifications and datasheets

[Eaton Specification Sheet - QBHW1015](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)