

Specifications



Eaton QBHW1030

Eaton QB thermal magnetic circuit breaker, Quicklag industrial thermal-magnetic circuit breaker, 35 A, 22 kAIC, Single-pole, 120/240 V, Non-Interchangeable, Q17, QBHW

Physical Attributes

CIRCUIT BREAKER TYPE	QBHW
MOUNTING METHOD	Bolt-on
NUMBER OF POLES	Single-pole
TYPE	Quicklag industrial thermal-magnetic circuit breaker

General specifications

PRODUCT NAME	Eaton QB thermal magnetic circuit breaker
CATALOG NUMBER	QBHW1030
UPC	786679392157
PRODUCT LENGTH/DEPTH	0.3 in
PRODUCT HEIGHT	0.5 in
PRODUCT WIDTH	0.1 in
PRODUCT WEIGHT	0.35 lb
WARRANTY	1 year
CERTIFICATIONS	UL Listed CSA Certified
CATALOG NOTES	HACR rated



Powering Business Worldwide