

# Specifications

## Eaton QBHW2040

Quicklag Industrial Thermal-Magnetic Circuit Breaker, Two-pole, 40A, 22 kAIC, 120/240V , Bolt-on



### General specifications

<b>PRODUCT NAME</b>	Eaton QB thermal magnetic circuit breaker
<b>CATALOG NUMBER</b>	QBHW2040
<b>UPC</b>	786679392751
<b>PRODUCT LENGTH/DEPTH</b>	2.9 in
<b>PRODUCT HEIGHT</b>	2.9 in
<b>PRODUCT WIDTH</b>	2 in
<b>PRODUCT WEIGHT</b>	0.65 lb
<b>WARRANTY</b>	1 year
<b>CERTIFICATIONS</b>	UL Listed CSA Certified
<b>CATALOG NOTES</b>	HACR rated



*Powering Business Worldwide*

## Physical Attributes

CIRCUIT BREAKER TYPE	QBHW
MOUNTING METHOD	Bolt-on
NUMBER OF POLES	Two-pole
TYPE	Quicklag

## Performance Ratings

AMPERAGE RATING	40 A
INTERRUPT RATING	22 kAIC
TRIP TYPE	Non-Interchangeable
VOLTAGE RATING	120/240 V

## Miscellaneous

QUANTITY	7
----------	---

## Resources

SPECIFICATIONS AND DATASHEETS	<a href="#">Eaton Specification Sheet - QBHW2040</a>
-------------------------------	--

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.



# Specifications

## Eaton QBHW2040

Quicklag Industrial Thermal-Magnetic Circuit Breaker, Two-pole, 40A, 22 kAIC, 120/240V , Bolt-on



### General specifications

<b>PRODUCT NAME</b>	Eaton QB thermal magnetic circuit breaker
<b>CATALOG NUMBER</b>	QBHW2040
<b>UPC</b>	786679392751
<b>PRODUCT LENGTH/DEPTH</b>	2.9 in
<b>PRODUCT HEIGHT</b>	2.9 in
<b>PRODUCT WIDTH</b>	2 in
<b>PRODUCT WEIGHT</b>	0.65 lb
<b>WARRANTY</b>	1 year
<b>CERTIFICATIONS</b>	UL Listed CSA Certified
<b>CATALOG NOTES</b>	HACR rated



*Powering Business Worldwide*

## Physical Attributes

CIRCUIT BREAKER TYPE	QBHW
MOUNTING METHOD	Bolt-on
NUMBER OF POLES	Two-pole
TYPE	Quicklag

## Performance Ratings

AMPERAGE RATING	40 A
INTERRUPT RATING	22 kAIC
TRIP TYPE	Non-Interchangeable
VOLTAGE RATING	120/240 V

## Miscellaneous

QUANTITY	7
----------	---

## Resources

SPECIFICATIONS AND DATASHEETS	<a href="#">Eaton Specification Sheet - QBHW2040</a>
-------------------------------	--

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

