

# Eaton QBHW2100

Catalog Number: QBHW2100

Quicklag Industrial Thermal-Magnetic Circuit Breaker, Two-pole,  
100A, 22 kAIC, 120/240V , Bolt-on

## General specifications



|   |                       |
|---|-----------------------|
| <b>Product Name</b>                       | <b>Catalog Number</b> |
| Eaton QB thermal magnetic circuit breaker | QBHW2100              |
|   | UPC                   |
|   | 786679393109          |
| <b>Product Length/Depth</b>               | <b>Product Height</b> |
| 4 in                                      | 4.8 in                |
| <b>Product Width</b>                      | <b>Product Weight</b> |
| 2.2 in                                    | 0.8 lb                |
| <b>Warranty</b>                           | <b>Certifications</b> |
| 1 year                                    | CSA Certified         |
|   | UL Listed             |
| <b>Catalog Notes</b>                      |                       |
| HACR rated                                |                       |

## Physical Attributes

### Circuit breaker type

QBHW

### Mounting Method

Bolt-on

### Number of poles

Two-pole

### Type

Quicklag

## Performance Ratings

### Amperage Rating

100 A

### Interrupt rating

22 kAIC

### Trip Type

Non-Interchangeable

### Voltage rating

120/240 V

## Miscellaneous

### Quantity

7

## Resources

### Brochures

[Loadcenters and Circuit Breakers](#)

### Catalogs

[Eaton's Volume 4—Circuit Protection](#)

### Specifications and datasheets

[Eaton Specification Sheet - QBHW2100](#)

[Circuit Breaker Time/Current Curves For QUICKLAG. Industrial Circuit Breakers](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)