

Specifications

Eaton QBHW2100

Quicklag Industrial Thermal-Magnetic Circuit Breaker, Two-pole, 100A, 22 kAIC, 120/240V , Bolt-on



General specifications

PRODUCT NAME	Eaton QB thermal magnetic circuit breaker
CATALOG NUMBER	QBHW2100
UPC	786679393109
PRODUCT LENGTH/DEPTH	4 in
PRODUCT HEIGHT	4.8 in
PRODUCT WIDTH	2.2 in
PRODUCT WEIGHT	0.8 lb
WARRANTY	1 year
CERTIFICATIONS	CSA Certified UL Listed
CATALOG NOTES	HACR rated



Powering Business Worldwide

Physical Attributes

CIRCUIT BREAKER TYPE	QBHW
MOUNTING METHOD	Bolt-on
NUMBER OF POLES	Two-pole
TYPE	Quicklag

Performance Ratings

AMPERAGE RATING	100 A
INTERRUPT RATING	22 kAIC
TRIP TYPE	Non-Interchangeable
VOLTAGE RATING	120/240 V

Miscellaneous

QUANTITY	7
----------	---

Resources

SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - QBHW2100
-------------------------------	--

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

