

Specifications



Eaton QBHW3060H

Eaton Quicklag Industrial Thermal-Magnetic Circuit Breaker, Three-pole, 60A, 22 kAIC, 240V, Bolt-on

Physical Attributes

CIRCUIT BREAKER TYPE	QBHW
MOUNTING METHOD	Bolt-on
NUMBER OF POLES	Three-pole
TYPE	Quicklag

General specifications

PRODUCT NAME	Eaton QB thermal magnetic circuit breaker
CATALOG NUMBER	QBHW3060H
UPC	786679393505
PRODUCT LENGTH/DEPTH	2.9 in
PRODUCT HEIGHT	2.3 in
PRODUCT WIDTH	3 in
PRODUCT WEIGHT	1.05 lb
WARRANTY	1 year
CERTIFICATIONS	UL Listed CSA Certified
CATALOG NOTES	HACR rated



Powering Business Worldwide