# Specifications









## Eaton QBHW3100H

Eaton Quicklag Industrial Thermal-Magnetic Circuit Breaker, Three-pole, 100A, 22 kAIC, 240V, Bolt-on

| General specifications | |
|---|---|
| **PRODUCT NAME** | Eaton QB thermal magnetic circuit breaker |
| **CATALOG NUMBER** | QBHW3100H |
| **UPC** | 786679393659 |
| **PRODUCT LENGTH/DEPTH** | 2.9 in |
| **PRODUCT HEIGHT** | 3 in |
| **PRODUCT WIDTH** | 2.9 in |
| **PRODUCT WEIGHT** | 1.1 lb |
| **WARRANTY** | 1 year |
| **CERTIFICATIONS** | UL Listed<br>CSA Certified |
| **CATALOG NOTES** | HACR rated |

Powering Business Worldwide

## Physical Attributes

| | |
|---|---|
| **CIRCUIT BREAKER TYPE** | QBHW |
| **MOUNTING METHOD** | Bolt-on |
| **NUMBER OF POLES** | Three-pole |
| **TYPE** | Quicklag |

## Performance Ratings

| | |
|---|---|
| **AMPERAGE RATING** | 100 A |
| **INTERRUPT RATING** | 22 kAIC |
| **TRIP TYPE** | Non-Interchangeable |
| **VOLTAGE RATING** | 240 V - 240 V |

## Miscellaneous

| | |
|---|---|
| **QUANTITY** | 32 |

## Resources

| | |
|---|---|
| CATALOGS | Circuit Protection, Miniature Circuit Breakers and Supplementary Protectors, Volume 4, Tab 1 |
| SPECIFICATIONS AND DATASHEETS | Eaton Specification Sheet - QBHW3100H |

| | |
|---|---|
| **PROJECT NAME:** | |
| **PROJECT NUMBER:** | |
| **PREPARED BY:** | |
| **DATE:** | |

**Eaton Corporation plc** Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

# Specifications









## Eaton QBHW3100H

Eaton Quicklag Industrial Thermal-Magnetic Circuit Breaker, Three-pole, 100A, 22 kAIC, 240V, Bolt-on

| General specifications | |
|---|---|
| **PRODUCT NAME** | Eaton QB thermal magnetic circuit breaker |
| **CATALOG NUMBER** | QBHW3100H |
| **UPC** | 786679393659 |
| **PRODUCT LENGTH/DEPTH** | 2.9 in |
| **PRODUCT HEIGHT** | 3 in |
| **PRODUCT WIDTH** | 2.9 in |
| **PRODUCT WEIGHT** | 1.1 lb |
| **WARRANTY** | 1 year |
| **CERTIFICATIONS** | UL Listed<br>CSA Certified |
| **CATALOG NOTES** | HACR rated |

Powering Business Worldwide

## Physical Attributes

| | |
|---|---|
| **CIRCUIT BREAKER TYPE** | QBHW |
| **MOUNTING METHOD** | Bolt-on |
| **NUMBER OF POLES** | Three-pole |
| **TYPE** | Quicklag |

## Performance Ratings

| | |
|---|---|
| **AMPERAGE RATING** | 100 A |
| **INTERRUPT RATING** | 22 kAIC |
| **TRIP TYPE** | Non-Interchangeable |
| **VOLTAGE RATING** | 240 V - 240 V |

## Miscellaneous

| | |
|---|---|
| **QUANTITY** | 32 |

## Resources

| | |
|---|---|
| CATALOGS | Circuit Protection, Miniature Circuit Breakers and Supplementary Protectors, Volume 4, Tab 1 |
| SPECIFICATIONS AND DATASHEETS | Eaton Specification Sheet - QBHW3100H |

| | |
|---|---|
| **PROJECT NAME:** | |
| **PROJECT NUMBER:** | |
| **PREPARED BY:** | |
| **DATE:** | |

**Eaton Corporation plc** Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.