

Eaton QC2010

Catalog Number: QC2010

Eaton Quicklag Type QC Industrial Thermal-Magnetic Circuit Breaker, Industrial circuit breaker, 10 A, 10 kAIC, Two-pole, 120/240 V, Thermal-magnetic, Cable-in/cable-out, QC, Non-interchangeable



General specifications

Product Name	Catalog Number
Eaton QC thermal magnetic circuit breaker	QC2010
	UPC
	786679309285
Product Length/Depth	Product Height
3.8 in	4.8 in
Product Width	Product Weight
2.2 in	0.65 lb
Warranty	Certifications
1 year	CSA Certified
	UL Listed

Physical Attributes

Circuit breaker type

QC

Connection

Cable-in/cable-out

Number of poles

Two-pole

Type

Industrial circuit breaker

Performance Ratings

Amperage Rating

10 A

Interrupt rating

10 kAIC

Trip Type

T268

Voltage rating

120/240 V

Miscellaneous

Options

Non-interchangeable

Resources

Specifications and datasheets

[Eaton Specification Sheet - QC2010](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)