

Eaton QC2030

Catalog Number: QC2030

Eaton Quicklag Type QC Industrial Thermal-Magnetic Circuit Breaker, Industrial circuit breaker, 30 A, 10 kAIC, Two-pole, 120/240 V, Thermal-magnetic, QC, Non-interchangeable

General specifications

| | |
|---|-----------------------|
| Product Name | Catalog Number |
| Eaton QC thermal magnetic circuit breaker | QC2030 |
| | UPC |
| | 786679309469 |
| Product Length/Depth | Product Height |
| 3.9 in | 1 in |
| Product Width | Product Weight |
| 3.125 in | 0.75 lb |
| Warranty | Certifications |
| 1 year | UL Listed |
| | CSA Certified |



Physical Attributes

Circuit breaker type

QC

Number of poles

Two-pole

Type

Industrial circuit breaker

Performance Ratings

Amperage Rating

30 A

Interrupt rating

10 kAIC

Trip Type

Thermal-magnetic

Voltage rating

120/240 V

Miscellaneous

Options

Non-interchangeable

Resources

Specifications and datasheets

[Eaton Specification Sheet - QC2030](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)