

# Eaton QC3040H

Catalog Number: QC3040H

Eaton Quicklag Type QC Industrial Thermal-Magnetic Circuit Breaker, Industrial circuit breaker, 40 A, 10 kAIC, Three-pole, 240 V, Thermal-magnetic, QC, Non-interchangeable

## General specifications



|   |                       |
|---|-----------------------|
| <b>Product Name</b>                       | <b>Catalog Number</b> |
| Eaton QC thermal magnetic circuit breaker | QC3040H               |
|   | UPC                   |
|   | 786679240144          |
| <b>Product Length/Depth</b>               | <b>Product Height</b> |
| 3.8 in                                    | 4.9 in                |
| <b>Product Width</b>                      | <b>Product Weight</b> |
| 3.1 in                                    | 1.2 lb                |
| <b>Warranty</b>                           | <b>Certifications</b> |
| 1 year                                    | UL Listed             |
|   | CSA Certified         |

## Physical Attributes

### Circuit breaker type

QC

### Number of poles

Three-pole

### Type

Industrial circuit breaker

## Performance Ratings

### Amperage Rating

40 A

### Interrupt rating

10 kAIC

### Trip Type

Thermal-magnetic

### Voltage rating

240 V - 240 V

## Miscellaneous

### Options

Non-interchangeable

## Resources

### Specifications and datasheets

[Eaton Specification Sheet - QC3040H](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

# Eaton QC3040H

Catalog Number: QC3040H

Eaton Quicklag Type QC Industrial Thermal-Magnetic Circuit Breaker, Industrial circuit breaker, 40 A, 10 kAIC, Three-pole, 240 V, Thermal-magnetic, QC, Non-interchangeable

## General specifications



|   |                       |
|---|-----------------------|
| <b>Product Name</b>                       | <b>Catalog Number</b> |
| Eaton QC thermal magnetic circuit breaker | QC3040H               |
|   | UPC                   |
|   | 786679240144          |
| <b>Product Length/Depth</b>               | <b>Product Height</b> |
| 3.8 in                                    | 4.9 in                |
| <b>Product Width</b>                      | <b>Product Weight</b> |
| 3.1 in                                    | 1.2 lb                |
| <b>Warranty</b>                           | <b>Certifications</b> |
| 1 year                                    | UL Listed             |
|   | CSA Certified         |

## Physical Attributes

### Circuit breaker type

QC

### Number of poles

Three-pole

### Type

Industrial circuit breaker

## Performance Ratings

### Amperage Rating

40 A

### Interrupt rating

10 kAIC

### Trip Type

Thermal-magnetic

### Voltage rating

240 V - 240 V

## Miscellaneous

### Options

Non-interchangeable

## Resources

### Specifications and datasheets

[Eaton Specification Sheet - QC3040H](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)