

Specifications



Eaton QC3040H

Eaton Quicklag Type QC Industrial Thermal-Magnetic Circuit Breaker, Industrial circuit breaker, 40 A, 10 kAIC, Three-pole, 240 V, Thermal-magnetic, QC, Non-interchangeable

General specifications

PRODUCT NAME	Eaton QC thermal magnetic circuit breaker
CATALOG NUMBER	QC3040H
UPC	786679240144
PRODUCT LENGTH/DEPTH	3.8 in
PRODUCT HEIGHT	4.9 in
PRODUCT WIDTH	3.1 in
PRODUCT WEIGHT	1.2 lb
WARRANTY	1 year
CERTIFICATIONS	UL Listed CSA Certified

Physical Attributes	
CIRCUIT BREAKER TYPE	QC
NUMBER OF POLES	Three-pole
TYPE	Industrial circuit breaker

Performance Ratings	
AMPERAGE RATING	40 A
INTERRUPT RATING	10 kAIC
TRIP TYPE	T268
VOLTAGE RATING	240 V - 240 V

Miscellaneous	
OPTIONS	Non-interchangeable

Resources	
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - QC3040H

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark. Follow us on social media to get the latest product and support information.
All other trademarks are property of their respective owners.

