

Eaton QC3050H

Catalog Number: QC3050H

Eaton Quicklag Type QC Industrial Thermal-Magnetic Circuit Breaker, Industrial circuit breaker, 50 A, 10 kAIC, Three-pole, 240 V, Thermal-magnetic, QC, Non-interchangeable

General specifications



| | |
|---|-----------------------|
| Product Name | Catalog Number |
| Eaton QC thermal magnetic circuit breaker | QC3050H |
| | UPC |
| | 786679240182 |
| Product Length/Depth | Product Height |
| 3.9 in | 4.7 in |
| Product Width | Product Weight |
| 3.2 in | 1.15 lb |
| Warranty | Certifications |
| 1 year | UL Listed |
| | CSA Certified |

Physical Attributes

Circuit breaker type

QC

Number of poles

Three-pole

Type

Industrial circuit breaker

Performance Ratings

Amperage Rating

50 A

Interrupt rating

10 kAIC

Trip Type

Thermal-magnetic

Voltage rating

240 V - 240 V

Miscellaneous

Options

Non-interchangeable

Resources

Brochures

[Loadcenters and Circuit Breakers](#)

Catalogs

[Eaton's Volume 4—Circuit Protection](#)

Specifications and datasheets

[Circuit Breaker Time/Current Curves For QUICKLAG. Industrial Circuit Breakers](#)

[Eaton Specification Sheet - QC3050H](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

Eaton QC3050H

Catalog Number: QC3050H

Eaton Quicklag Type QC Industrial Thermal-Magnetic Circuit Breaker, Industrial circuit breaker, 50 A, 10 kAIC, Three-pole, 240 V, Thermal-magnetic, QC, Non-interchangeable

General specifications



| | |
|---|-----------------------|
| Product Name | Catalog Number |
| Eaton QC thermal magnetic circuit breaker | QC3050H |
| | UPC |
| | 786679240182 |
| Product Length/Depth | Product Height |
| 3.9 in | 4.7 in |
| Product Width | Product Weight |
| 3.2 in | 1.15 lb |
| Warranty | Certifications |
| 1 year | UL Listed |
| | CSA Certified |

Physical Attributes

Circuit breaker type

QC

Number of poles

Three-pole

Type

Industrial circuit breaker

Performance Ratings

Amperage Rating

50 A

Interrupt rating

10 kAIC

Trip Type

Thermal-magnetic

Voltage rating

240 V - 240 V

Miscellaneous

Options

Non-interchangeable

Resources

Brochures

[Loadcenters and Circuit Breakers](#)

Catalogs

[Eaton's Volume 4—Circuit Protection](#)

Specifications and datasheets

[Circuit Breaker Time/Current Curves For QUICKLAG. Industrial Circuit Breakers](#)

[Eaton Specification Sheet - QC3050H](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)