



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



QC3050H Type QC BRKR 3P 50A 240VAC Max 10kaic *Eaton Corp*

| | |
|------------------|--|
| Catalog Number | QC3050H |
| Manufacturer | Eaton Corp |
| Description | Thermal Magnetic Circuit Breaker, 50 A, Non-Interchangeable Tripping Mechanism, Cable-In/Cable-Out Terminal, Panel Mount, 240 V Ac, 4.7 In Overall Height, 3.9 In Overall Length |
| Weight per unit | 1.2 (lbs/each) |
| Product Category | 3 Pole Din Rail Mount Circuit |

Features

| | |
|------------|-----------------------------------|
| dimensions | 3.9000 IN X 3.2000 IN X 4.7000 IN |
| Poles | 3 |

Descriptions

| | |
|------------------------|---|
| Description | TYPE QC BRKR 3P 50A 240VAC MAX 10KAIC |
| extra long description | ETN QC3050H TYPE QC BREAKER 3P 50A |
| Features | Eaton has a wide selection of UL rated miniature circuit breakers for loadcenters, fuseboxes, or similar devices. Each pole provides steel frame calibration and arc chutes with 5 - 100A continuous in one-, two-, and three-pole designs. A full-range of accessories expand customization options, including various mounting and ring tung termination options. |

Manufacturer Information

| | |
|------|----------------|
| GTIN | 00786679240182 |
| UPC | 786679240182 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|-----------------------------------|
| Category Description | MOLDED CASE BREAKERS |
| Type | Thermal magnetic circuit breakers |

Packaging

| | |
|-----------------|------|
| Carton | 1 |
| Package | 8 |
| Weight Per each | 1.15 |

Uses, Certifications, and Standards

| | |
|-------------|--|
| Application | Generation - Conventional Energy - Conventional Energy Generation - Renewable Energy - Alternative Energy Marine Vessels and Equipment - Marine Vessels and Equipment - Other Datacenters - IT Space: CI and Hyper Converged Other |
| standard | UL Listed, CSA Certified |