

Eaton QCF1015

Catalog Number: QCF1015

Eaton Quicklag Type QCF 1/2-inch Industrial Thermal-Magnetic Circuit Breaker, Industrial circuit breaker, 15 A, 10 kAIC, Single-pole, 120/240 V, Thermal-magnetic, Cable-in/cable-out, QCF, Non-interchangeable



General specifications

Product Name	Catalog Number
Eaton QCF thermal magnetic circuit breaker	QCF1015
	UPC
	786679143025
Product Length/Depth	Product Height
4.6 in	1.2 in
Product Width	Product Weight
3 in	0.3 lb
Warranty	Certifications
1 year	UL Listed
	CSA Certified

Catalog Notes

Standard Breaker terminals are box type lugs. Switching duty rated for fluorescent lighting applications.

Physical Attributes

Circuit breaker type

QCF

Connection

Cable-in/cable-out

Mounting Method

Front

Number of poles

Single-pole

Type

Industrial circuit breaker

Performance Ratings

Amperage Rating

15 A

Interrupt rating

10 kAIC

Trip Type

Thermal-magnetic

Voltage rating

120/240 V

Miscellaneous

Options

Non-interchangeable

Resources

Brochures

[Loadcenters and Circuit Breakers](#)

Catalogs

[Eaton's Volume 4—Circuit Protection](#)

Specifications and datasheets

[Eaton Specification Sheet - QCF1015](#)

[Circuit Breaker Time/Current Curves For QUICKLAG. Industrial Circuit Breakers](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia