

# Eaton QCF1030

Catalog Number: QCF1030

Eaton Quicklag Type QCF 1/2-inch Industrial Thermal-Magnetic Circuit Breaker, Industrial circuit breaker, 30 A, 10 kAIC, Single-pole, 120/240 V, Thermal-magnetic, Cable-in/cable-out, QCF, Non-interchangeable



## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton QCF thermal magnetic circuit breaker	QCF1030
	UPC
	786679143124
<b>Product Length/Depth</b>	<b>Product Height</b>
3 in	1 in
<b>Product Width</b>	<b>Product Weight</b>
3 in	0.301 lb
<b>Warranty</b>	<b>Certifications</b>
1 year	CSA Certified
	UL Listed

## Catalog Notes

Standard Breaker terminals are box type lugs.

## Physical Attributes

### Circuit breaker type

QCF

### Connection

Cable-in/cable-out

### Mounting Method

Front

### Number of poles

Single-pole

### Type

Industrial circuit breaker

## Performance Ratings

### Amperage Rating

30 A

### Interrupt rating

10 kAIC

### Trip Type

Thermal-magnetic

### Voltage rating

120/240 V

## Miscellaneous

### Options

Non-interchangeable

## Resources

### Brochures

[Loadcenters and Circuit Breakers](#)

### Catalogs

[Eaton's Volume 4—Circuit Protection](#)

### Specifications and datasheets

[Eaton Specification Sheet - QCF1030](#)

[Circuit Breaker Time/Current Curves For QUICKLAG. Industrial Circuit Breakers](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://Eaton.com/socialmedia)