

# Specifications



## Eaton QCR2030

Eaton Quicklag Type QCR 1/2-inch Industrial Thermal-Magnetic Circuit Breaker, Industrial circuit breaker, 30 A, 10 kAIC, Two-pole, 120/240 V, Thermal-magnetic, Cable-in/cable-out, QCR, Fixed

### General specifications

<b>PRODUCT NAME</b>	Eaton QCR thermal magnetic circuit breaker
<b>CATALOG NUMBER</b>	QCR2030
<b>UPC</b>	786679144343
<b>PRODUCT LENGTH/DEPTH</b>	4.6 in
<b>PRODUCT HEIGHT</b>	1.2 in
<b>PRODUCT WIDTH</b>	3.3 in
<b>PRODUCT WEIGHT</b>	0.5 lb
<b>WARRANTY</b>	1 year
<b>COMPLIANCES</b>	HACR Rated
<b>CERTIFICATIONS</b>	CSA Certified UL Listed
<b>CATALOG NOTES</b>	Standard breaker terminals are box type lugs.



Powering Business Worldwide

## Physical Attributes

<b>CIRCUIT BREAKER TYPE</b>	QCR
<b>CONNECTION</b>	Cable-in/cable-out
<b>MOUNTING METHOD</b>	Rear
<b>NUMBER OF POLES</b>	Two-pole
<b>TERMINALS</b>	Fixed
<b>TYPE</b>	Industrial circuit breaker

## Performance Ratings

<b>AMPERAGE RATING</b>	30 A
<b>INTERRUPT RATING</b>	10 kAIC
<b>TRIP TYPE</b>	T268
<b>VOLTAGE RATING</b>	120/240 V

## Resources

**SPECIFICATIONS AND DATASHEETS** [Eaton Specification Sheet - QCR2030](#)

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark. Follow us on social media to get the latest product and support information.  
All other trademarks are property of their respective owners.

