



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



QTP4X32T8UNVISNS 32WT8 Uni Volt Electronic Ballast 4lamp

Sylvania-Ledvance

Catalog Number	QTP4X32T8UNVISNS
Manufacturer	Sylvania-Ledvance
Description	OBS49947 QTP4X32T8UNVISNSC 4 Lamp 32WT8 Instant Start Electronic Ballast, Universal Voltage, Normal Ballast Factor, 10 PK
Weight per unit	0.9500 (lbs/each)
Product Category	Electronic Linear Fluorescent

Features

amperage rating	0.27
Ballast Factor	88
dimnable	False
Lamp Type	FO32/XP
Minimum Starting Temperature	-20.000000000000000
Number of Lamps	4
Power Factor	>0.97
start type	Instant Start
total harmonic distortion	<10
Voltage Rating	120
Wattage	32

Dimensions and Weight

Height	1.1810000000000000
Length	9.4690000000000000
Width	1.6810000000000000

Descriptions

Description	32WT8 UNI VOLT ELECTRONIC BALLAST 4LAMP
extra long description	SYL QTP-4x32T8/UNV-ISN-SC/49947 QTP
Long Description	OBS49947 QTP4x32T8UNVISNSC 4 lamp 32wT8 Instant Start electronic ballast, universal voltage, normal ballast factor, 10 pk
Product Type	QTP4X32T8UNVISNSC 10/CS 1/Sku
Special Features	NO

Manufacturer Information

Brand	Ledvance LLC
GTIN	00046135499470
Manufacturers Part Number	QTP-4X32T8/UNV-ISN-SC/49947
UPC	046135499470

Taxonomies, Classifications, and Categories

Category Description	ELECTRONIC BALLAST
Type	Ballasts And Lighting Controls



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Package	10
Weight Per each	0.95

Uses, Certifications, and Standards

Application	lighting
Mounting	Tabbed
standard	FCC 47 CFR Part 18, Non-Consumer