



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3325 Clay Avenue
76711-0000, TX Waco
Phone: 254-752-3331
Fax: 254-752-3460



ROS20 #8-2/0 Awg Direct Burial "Cold Roll-On" Splice

Nsi Industries

Catalog Number	ROS20
Manufacturer	Nsi Industries
Description	Easy-Splice Roll On, Black Insulation Color, Sealing Strip, -40 °C Operating Temperature, +90 °C Operating Temperature, 5 In (Connector);8 In (Sleeve) Overall Length, 1000 V, 0.17 LB
Weight per unit	0.1700 (lbs/each)
Product Category	Splicing & Terminating Kits

Features

Cable Size	8-2/0 AWG
Cable Type	Class A-B
insulation	EPDM Elastomer
Material	EPDM RUBBER
Voltage Rating	1000 V
Warranty	1 YEAR

Material, Color, and Finish

Color	Black
-------	-------

Descriptions

Description	#8-2/0 AWG DIRECT BURIAL "COLD ROLL-ON" SPLICE
extra long description	NSI ROS-2/0 Easy-Splice Roll On Spl
Special Features	Easy Roll-On Way To Insulate And Seal Cable - Made Of EPDM Elastomer

Manufacturer Information

GTIN	00662381123350
UPC	662381123350

Taxonomies, Classifications, and Categories

Category Description	SPLICE KITS
Type	Roll-On Splice Kits

Packaging

Carton	6
Weight Per each	0.17

Uses, Certifications, and Standards

Application	Splicing Wire
Operating Temperature standard	-40 C To 90 C ANSI C119.1-1986 Qualified, UL 486D