

Eaton R9000 E

Catalog Number: R9000 E

Eaton B-Line series busbar and termination cabinets, 800 A, 3R, Underground, ANSI 61 gray painted, 065 kAIC, 4 Studs / Ø, (3) #4 - 600 MCM, Galvanized steel, 3 wires, 1 phase or 3 phase, Termination point before busbar



General specifications

Product Name	Catalog Number
Eaton B-Line series busbar and termination cabinets	R9000 E
	UPC
	782051531862
Product Length/Depth	Product Height
11 in	52 in
Product Width	Product Weight
18 in	123 lb
Compliances	Certifications
EUSERC Approved	UL

Electrical specifications

Amperage Rating

800 A

Phase

Single-phase, three-phase

Interrupt rating

65 kAIC

Material/finish

Material

Galvanized steel

Finish

ANSI 61 gray paint

Model

Number of wires

3

Feed type

Underground

Mounting method

Surface

Line lug size

4 studs/Ø

Load lug size

(3) #4 - 600 MCM

Special features

Used as a termination point before busse

Standards

Degree of protection

3R

Resources

Catalogs

[bussed gutters](#)

[universal bussed gutters](#)

Specifications and datasheets

[Eaton Specification Sheet - R9000 E](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)