



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1105 West Sanger
88240-0000, NM Hobbs
Phone: 575-397-2122
Fax: 575-397-2178



RC1010FL 12-10 Ins Nylon Spade Term

Abb Installation Products, Inc

Catalog Number	RC1010FL
Manufacturer	Abb Installation Products, Inc
Description	Nylon Insulated Locking Fork Terminal, Length 1.00 Inches, Width .37 Inches, Maximum Insulation .210, Bolt Hole #10, Wire Range #12-#10 Awg, Color Yellow, Copper, Tin Plated
Weight per unit	0.0060 (lbs/each)
Product Category	Small Terminals & Connectors

Features

Material	Copper
Voltage Rating	600 V
Wire Size	12-10 AWG

Material, Color, and Finish

Color	Yellow
-------	--------

Descriptions

Description	12-10 INS NYLON SPADE TERM
extra long description	ABB RC10-10FL INSNYL LKG FORK TERM
Long Description	Nylon Insulated Locking Fork Terminal, Length 1.00 Inches, Width .37 Inches, Maximum Insulation .210, Bolt Hole #10, Wire Range #12-#10 AWG, Color Yellow, Copper, Tin Plated
Product Type	Insnyl LKG Fork Term 12-10 NO10 Yel
Special Features	Locking fork terminals have a specially designed tongue that lets them go on like a fork and stay on like a ring

Manufacturer Information

Brand	Sta-Kon
GTIN	00786210887531
Manufacturers Part Number	RC10-10FL
UPC	786210887531

Taxonomies, Classifications, and Categories

Category Description	TERMINALS
Type	Nylon Insulated Locking Fork Terminal

Availability

minimum qty	50
-------------	----

Packaging

Carton	50
Package	250
Weight Per each	0.006



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1105 West Sanger
88240-0000, NM Hobbs
Phone: 575-397-2122
Fax: 575-397-2178

Uses, Certifications, and Standards

standard

UL E9809 / UL E9809