



RDL6-BF-27K
RDL6-BF-30K
RDL6-BF-35K
RDL6-BF-41K
RDL6-BF-50K

LED DOWNLIGHTS (BAFFLE TRIM) - 5/6" ROUND

Isolated driver for improved thermal management.

ELECTRICAL SPECIFICATIONS:

- Voltage: 120VAC
- Wattage: 18W
- Power factor: >0.9
- Efficacy: 61LM/W, 66LM/W, 71LM/W, 72LM/W, 75LM/W

HOUSING SPECIFICATIONS:

- Die-cast aluminum with white powder coat finish (oil-rubbed Bronze Finish available in 3000k)
- Gasket: closed cell Neoprene foam gasket
- Isolated driver for improved thermal management
- Suitable for damp locations when gasket is used
- Maximum Ambient temperature: 104°F

CERTIFICATIONS: UL



DIMENSIONS:

5/6" DIAMETER

ACCESSORIES:



Includes medium base E-26 screw-in adaptor that fits any standard incandescent downlight

| MODEL | WATTS | VOLTAGE | LUMENS | COLOR TEMP |
|-------------|-------|---------|--------|------------|
| RDL6-BF-27K | 18W | 120VAC | 1102LM | 2700K |
| RDL6-BF-30K | 18W | 120VAC | 1204LM | 3000K |
| RDL6-BF-35K | 18W | 120VAC | 1280LM | 3500K |
| RDL6-BF-41K | 18W | 120VAC | 1300LM | 4100K |
| RDL6-BF-50K | 18W | 120VAC | 1350LM | 5000K |

LIGHTING SPECIFICATIONS:

- Dimming: dimmable
- Lens: 0.125" white translucent foam acrylic
- LED: EPISTAR chip (COB) and driver— 35,000-hour design life
- Total lumens: 1102LM/1204LM/1280LM/1300LM/1350LM
- Color temperature: 2700K/3000K/3500K/4100K/5000K
- CRI: 90

WARRANTY: 5 years





RDL6-BF-27K
RDL6-BF-30K
RDL6-BF-35K
RDL6-BF-41K
RDL6-BF-50K

LED DOWNLIGHTS (BAFFLE TRIM) - 5/6" ROUND

Isolated driver for improved thermal management.

ELECTRICAL SPECIFICATIONS:

- Voltage: 120VAC
- Wattage: 18W
- Power factor: >0.9
- Efficacy: 61LM/W, 66LM/W, 71LM/W, 72LM/W, 75LM/W

HOUSING SPECIFICATIONS:

- Die-cast aluminum with white powder coat finish (oil-rubbed Bronze Finish available in 3000k)
- Gasket: closed cell Neoprene foam gasket
- Isolated driver for improved thermal management
- Suitable for damp locations when gasket is used
- Maximum Ambient temperature: 104°F

CERTIFICATIONS: UL



DIMENSIONS:

5/6" DIAMETER

ACCESSORIES:



Includes medium base E-26 screw-in adaptor that fits any standard incandescent downlight

| MODEL | WATTS | VOLTAGE | LUMENS | COLOR TEMP |
|-------------|-------|---------|--------|------------|
| RDL6-BF-27K | 18W | 120VAC | 1102LM | 2700K |
| RDL6-BF-30K | 18W | 120VAC | 1204LM | 3000K |
| RDL6-BF-35K | 18W | 120VAC | 1280LM | 3500K |
| RDL6-BF-41K | 18W | 120VAC | 1300LM | 4100K |
| RDL6-BF-50K | 18W | 120VAC | 1350LM | 5000K |

LIGHTING SPECIFICATIONS:

- Dimming: dimmable
- Lens: 0.125" white translucent foam acrylic
- LED: EPISTAR chip (COB) and driver— 35,000-hour design life
- Total lumens: 1102LM/1204LM/1280LM/1300LM/1350LM
- Color temperature: 2700K/3000K/3500K/4100K/5000K
- CRI: 90

WARRANTY: 5 years

