

Specifications

Photo is representative

Eaton REN-20

Eaton Bussmann series REN fuse, time lag, non current-limiting, Industrial and commercial structures, 20 A, Class H, Non-indicating, Ferrule end x ferrule end, 10 kAIC, Standard, 10, 250 V

General specifications

PRODUCT NAME	Eaton Bussmann series REN fuse
CATALOG NUMBER	REN-20
UPC	051712100205
EAN	5027590098250
PRODUCT LENGTH/DEPTH	0.56 in
PRODUCT HEIGHT	2 in
PRODUCT WIDTH	0.56 in
PRODUCT WEIGHT	0.41 lb
WARRANTY	Not Applicable
COMPLIANCES	Not Applicable RoHS Compliant



Electrical rating

AMPERAGE RATING	20 A
INTERRUPT RATING	10 kAIC
VOLTAGE RATING	250 V

General information

CLASS	Class H
CONNECTION	Ferrule end x ferrule end
FUSE INDICATOR	Non-indicating
QUANTITY	10
SPECIAL FEATURES	Super lag, time lag, non current-limiting

Physical details

PACKAGING TYPE	Standard
----------------	----------

Resources

CATALOGS	Bussmann series complete full line catalog no. 1007 REN-20~SUPER LAG RENEWABLE FUSE 20/250
MULTIMEDIA	Bussmann series Fuseology

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc

Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights
Reserved.

Eaton is a registered trademark.

All other trademarks are property of
their respective owners.

Follow us on social media to get the latest
product and support information.

