

# Eaton REN-20

Catalog Number: REN-20

Eaton Bussmann series REN fuse, time lag, non current-limiting, Industrial and commercial structures, 20 A, Class H, Non-indicating, Ferrule end x ferrule end, 10 kAIC, Standard, 10, 250 V

## General specifications



Photo is representative

<b>Product Name</b>	<b>Catalog Number</b>
Eaton Bussmann series REN fuse	REN-20
<b>UPC</b>	<b>EAN</b>
051712100205	5027590098250
<b>Product Length/Depth</b>	<b>Product Height</b>
0.56 in	2 in
<b>Product Width</b>	<b>Product Weight</b>
0.56 in	0.41 lb
<b>Warranty</b>	<b>Compliances</b>
Not Applicable	Not Applicable RoHS Compliant

## Electrical rating

### Amperage Rating

20 A

### Interrupt rating

10 kAIC

### Voltage rating

250 V

## Physical details

### Packaging type

Standard

## General information

### Class

Class H

### Connection

Ferrule end x ferrule end

### Fuse indicator

Non-indicating

### Quantity

10

### Special features

Super lag, time lag, non current-limiting

## Resources

### Catalogs

[REN-20~SUPER LAG RENEWABLE FUSE 20/250](#)

[Bussmann series complete full line catalog no. 1007](#)

### Multimedia

[Bussmann series Fuseology](#)

### Specifications and datasheets

[Eaton Specification Sheet - REN-20](#)