

Eaton REN-40

Catalog Number: REN-40

Eaton Bussmann series REN fuse, time lag, non current-limiting, Industrial and commercial structures, 40 A, Class H, Non-indicating, 10 kAIC, Standard, 10, 250 V

General specifications



Product Name	Catalog Number
Eaton Bussmann series REN fuse	REN-40
UPC	EAN
051712100403	5027590182386
Product Length/Depth	Product Height
0.82 in	2.98 in
Product Width	Product Weight
0.82 in	0.12 lb
Warranty	Compliances
Not Applicable	Not Applicable

Product specifications

Fuse indicator

Non-indicating

Special features

Super lag, time lag, non current-limiting

Interrupt rating

10 kAIC

Type

Renewable fuse

Quantity

10

Class

Class H

Voltage rating

250 V

Application

Industrial and commercial structures

Amperage Rating

40 A

Packaging type

Standard

Resources

Catalogs

Bussmann series complete full line catalog no. 1007

REN-40-SUPER LAG RENEWABLE FUSE 40/250

Multimedia

Bussmann series Fuseology

Specifications and datasheets

Eaton Specification Sheet - REN-40



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia