

Eaton REN-50

Catalog Number: REN-50

Eaton Bussmann series REN fuse, time lag, non current-limiting, Industrial and commercial structures, 50 A, Class H, Non-indicating, Ferrule end x ferrule end, 10 kAIC, Standard, 10, 250 V

General specifications



Photo is representative

Product Name	Catalog Number
Eaton Bussmann series REN fuse	REN-50
UPC	EAN
051712100502	5027590465793
Product Length/Depth	Product Height
0.82 in	2.98 in
Product Width	Product Weight
0.82 in	0.12 lb
Warranty	Compliances
Not Applicable	Not Applicable

Electrical rating

Amperage Rating

50 A

Interrupt rating

10 kAIC

Voltage rating

250 V

Physical details

Packaging type

Standard

General information

Class

Class H

Connection

Ferrule end x ferrule end

Fuse indicator

Non-indicating

Quantity

10

Special features

Super lag, time lag, non current-limiting

Resources

Catalogs

[REN-50~SUPER LAG RENEWABLE FUSE 50/250](#)

[Bussmann series complete full line catalog no. 1007](#)

Multimedia

[Bussmann series Fuseology](#)

Specifications and datasheets

[Eaton Specification Sheet - REN-50](#)