

Eaton REN-60

Catalog Number: REN-60

Eaton Bussmann series REN fuse, time lag, non current-limiting, Industrial and commercial structures, 60 A, Class H, Non-indicating, Ferrule end x ferrule end, 10 kAIC, Standard, 10, 250 V

General specifications



Product Name	Catalog Number
Eaton Bussmann series REN fuse	REN-60
UPC	Product Length/Depth
051712100601	0.82 in
Product Height	Product Width
3 in	3 in
Product Weight	Warranty
1.4 lb	Not Applicable
Compliances	
Not Applicable	

Electrical rating

Amperage Rating

60 A

Interrupt rating

10 kAIC

Voltage rating

250 V

Physical details

Packaging type

Standard

General information

Class

Class H

Connection

Ferrule end x ferrule end

Fuse indicator

Non-indicating

Quantity

10

Special features

Super lag, time lag, non current-limiting

Resources

Catalogs

[Bussmann series complete full line catalog no. 1007](#)

[REN-60~SUPER LAG RENEWABLE FUSE 60/250](#)

Multimedia

[Bussmann series Fuseology](#)

Specifications and datasheets

[Eaton Specification Sheet - REN-60](#)

Eaton REN-60

Catalog Number: REN-60

Eaton Bussmann series REN fuse, time lag, non current-limiting, Industrial and commercial structures, 60 A, Class H, Non-indicating, Ferrule end x ferrule end, 10 kAIC, Standard, 10, 250 V

General specifications



Product Name	Catalog Number
Eaton Bussmann series REN fuse	REN-60
UPC	Product Length/Depth
051712100601	0.82 in
Product Height	Product Width
3 in	3 in
Product Weight	Warranty
1.4 lb	Not Applicable
Compliances	
Not Applicable	

Electrical rating

Amperage Rating

60 A

Interrupt rating

10 kAIC

Voltage rating

250 V

Physical details

Packaging type

Standard

General information

Class

Class H

Connection

Ferrule end x ferrule end

Fuse indicator

Non-indicating

Quantity

10

Special features

Super lag, time lag, non current-limiting

Resources

Catalogs

[Bussmann series complete full line catalog no. 1007](#)

[REN-60~SUPER LAG RENEWABLE FUSE 60/250](#)

Multimedia

[Bussmann series Fuseology](#)

Specifications and datasheets

[Eaton Specification Sheet - REN-60](#)