



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



RF150 1-1/2" Roof FLSHNG Steel *Bridgeport Fittings*

| | |
|------------------|---|
| Catalog Number | RF150 |
| Manufacturer | Bridgeport Fittings |
| Description | Flashing, Roof, Galvanized, Size 1 1/2 Inch |
| Weight per unit | 0.8680 (lbs/each) |
| Product Category | Entrance Caps & SVC Mast Accy |

Features

| | |
|-------------|-------------------|
| Cable Entry | Raised Mast entry |
| Material | Steel |
| media | Yes |

Material, Color, and Finish

| | |
|--------|------------|
| Finish | Galvanized |
|--------|------------|

Dimensions and Weight

| | |
|------|-------|
| Size | 1 1/2 |
|------|-------|

Descriptions

| | |
|------------------------|---|
| Description | 1-1/2" ROOF FLSHNG STEEL |
| extra long description | BPT RF-150 1-1/2" ROOF FLASHING |
| Long Description | Flashing, Roof, Galvanized, Size 1 1/2 Inch |
| Product Type | 1-1/2" Roof Flashing |
| Special Features | Galvanized - for use with galvanized, plastic, or cast iron electrical service mast |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Bridgeport |
| GTIN | 00781747141057 |
| Manufacturers Part Number | RF-150 |
| UPC | 781747141057 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|--|
| Category Description | SERVICE ENTRANCE FITTINGS: Weatherheads & Grounding Fittings & Ground Rods |
| Type | Roof Flashings |

Trade Size

| | |
|------------|-----|
| Trade Size | 1.5 |
|------------|-----|

Packaging

| | |
|-----------------|-------|
| Carton | 25 |
| Weight Per each | 0.868 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application

For use with galvanized, plastic, or cast iron electrical service mast. Fits flats to 40 Degrees.
