



FAN SPEED CONTROL DE-HUMMER, SINGLE POLE/3-WAY, TRI-COLOR (IVORY, WHITE, LIGHT ALMOND)

RHDH163PTC | radiant

FEATURES & BENEFITS

The radiant® collection is a step up from the standard with simple, classic options in wiring devices, home automation controls and screwless wall plates that complement today's homes.

radiant® Screwless Wall Plate not included.



- Part of the all new radiant® collection.
- Specially designed capacitive circuitry de-hummer feature virtually eliminates fan motor "hum" for quiet fan speed control.
- White LED glows when fan control is OFF for easy location in the dark.
- Constant memory returns the fan to previous level after a power failure.
- Single pole and 3-way operation.
- Works with standard 3-way switches and wiring.
- Screw-pressure-plate backwire terminals save time, space and money.

SPECIFICATIONS

GENERAL INFO

Color: Tri-Color (Ivory, White, Light Almond) Number Of Poles: Single Pole/3-Way Special Features: De-Hummer

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes

CSA Listing Info: C22.2 No. 184

CSA Standard: Yes

cULus: Yes UL Standard: Yes UN SPSC: 39121502

CONSTRUCTION INFORMATION

Component 4: 78500705369

DIMENSIONS

Depth (US): 1.25" Height (US): 4.25" Width (US): 1.75"

TECHNICAL INFORMATION

Amps: 1.6A Volts: 120V

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: CHINA