



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## RHL743PTC Rad CFL/Led SP/3W 450W Tri Color Ssl7a *Pass & Seymour/Legrand*

Catalog Number	RHL743PTC
Manufacturer	Pass & Seymour/Legrand
Description	7A SSL Led Dimmer, Tri-Color
Weight per unit	0.3083 (lbs/each)
Product Category	Lighting Dimmers

### Features

amperage rating	7
Connection Type	Screw Terminal
load	CFL, Incandescent, LED
media	Yes
Mounting Type	Box
Number of Gangs	1.0
Number of Switches	1.0
Switch Type	Slider, Paddle
Voltage	120.0 V
Voltage Rating	120
Wattage	700

### Material, Color, and Finish

Color	Ivory, Light Almond, White
Finish	Matte

### Descriptions

Description	RAD CFL/LED SP/3W 450W TRI COLOR SSL7A
extra long description	P&S RHL743PTC RAD CFL/LED SP/3W 450
Features	Locator Light
Long Description	7A SSL LED Dimmer, Tri-Color
Product Type	Rad CFL/Led SP/3W 450W, Tri CLR Ssl7a
Special Features	The radiant® collection is a step up from the standard with simple, classic options in wiring devices, home automation controls and screwless wall plates that complement today's homes. This dimmer is multi-location dimming with 3-Way wiring for simple installation.

### Manufacturer Information

Brand	LEGRAND-PASS & SEYMOUR
GTIN	00785007133875
Manufacturers Part Number	RHL743PTC
UPC	785007133875



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Type ..... Dimmer

## Trade Size

Amperage ..... 5.5

## Packaging

Carton ..... 1

Package ..... 24

Weight Per each ..... 0.3083

## Uses, Certifications, and Standards

Application ..... Residential

Enclosure ..... Thermoplastic

environmental conditions ..... Humidity: Less than 95% non condensing

Mounting ..... Box Mount

standard ..... UL, CULUS, CSA Listed, cULus, UL Listed