

# Specifications

## Eaton RI06P-W

Eaton rotary dimmer, Power failure memory, with preset, #16 AWG, 5A, 120V, Wire lead, Maintained closure, White, Indoor, 60 Hz, Incandescent, halogen, 0° to 40°C, Single-pole, three-way, Polycarbonate, 600W

### General specifications

<b>PRODUCT NAME</b>	Eaton rotary dimmer
<b>CATALOG NUMBER</b>	RI06P-W
<b>UPC</b>	032664699023
<b>PRODUCT LENGTH/DEPTH</b>	2.3 in
<b>PRODUCT HEIGHT</b>	4.75 in
<b>PRODUCT WIDTH</b>	3.06 in
<b>PRODUCT WEIGHT</b>	0.001 lb
<b>CERTIFICATIONS</b>	NOM cULus Listed
<b>PRODUCT TYPE</b>	Rotary dimmer



Powering Business Worldwide

## Product specifications

<b>FREQUENCY RATING</b>	60 Hz
<b>SPECIAL FEATURES</b>	Power failure memory, with preset
<b>AMPERAGE RATING</b>	5 A
<b>VOLTAGE RATING</b>	120 V
<b>ALLOWABLE WIRE SIZE</b>	#16 AWG
<b>OPERATING TEMPERATURE</b>	0 to 40 °C
<b>WIRING METHOD</b>	Wire lead
<b>WATTAGE</b>	600 W
<b>ENVIRONMENTAL CONDITIONS</b>	Indoor
<b>SWITCH TYPE</b>	Single-pole, three-way
<b>MOUNTING METHOD</b>	Flush
<b>CLOSURE TYPE</b>	Maintained
<b>LOAD TYPE</b>	INC HAL
<b>MATERIAL</b>	Polycarbonate
<b>COLOR</b>	White

## Resources

INSTALLATION VIDEOS	<a href="#">How to install Eaton's universal slide dimmers</a>
SPECIFICATIONS AND DATASHEETS	<a href="#">Eaton Specification Sheet - RI06P-W</a> <a href="#">Rotary dimmers and fan controls spec sheet</a>

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



**Eaton Corporation plc** Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

