


| SPECIFICATIONS                    |                                   |
|-----------------------------------|-----------------------------------|
| CONTACT CARRIER MATERIAL/COLOR    | NYLON OR TPU/YELLOW               |
| MOLDED HEAD MATERIAL/COLOR        | TPU/RED                           |
| CONTACT MATERIAL/PLATING          | BRASS/GOLD                        |
| COUPLING NUT MATERIAL/PLATING     | BRASS/NICKEL                      |
| RATED CURRENT [A]                 | 4.0 A                             |
| RATED VOLTAGE [V]                 | 250 VAC/300 VDC                   |
| OUTER CABLE JACKET MATERIAL/COLOR | PVC/RED                           |
| CONDUCTOR INSULATION MATERIAL     | PVC                               |
| NUMBER OF CONDUCTORS [AWG]        | 4x18 AWG                          |
| TEMPERATURE RANGE                 | -40°C to +105°C (-40°F to +221°F) |
| PROTECTION CLASS                  | MEETS NEMA 1,3,4,6P AND IEC IP68  |



| CABLE LENGTH | TOLERANCE *   |
|--------------|---|
| ALL LENGTHS  | + 4% (OR 50mm) OF LENGTH<br>- 0% (OR 0mm) OF LENGTH<br>WHICHEVER IS GREATER |
| STRIP LENGTH | TOLERANCE *   |
| 0-7mm        | ±0.5mm  |
| 8-29mm       | ±1.0mm  |
| 30-49mm      | ±2.0mm  |
| 50-69mm      | ±3.0mm  |
| 70-100mm     | ±4.0mm  |
| OVER 100mm   | ±5.0mm  |

\* UNLESS OTHERWISE SPECIFIED


NOTES:

- "\*" INDICATES CABLE LENGTH IN METERS. CONTACT TURCK TO ORDER SPECIFIC LENGTHS.
- "/CS11298" DESIGNATES RED, PVC CABLE (10150896), 4x18 AWG, WITH RED MOLDED PLUG BODIES.


SOURCE DRAWING - FOR REFERENCE ONLY

|                   |   |  |  |   |
|-------------------|---|--|--|---|
| RELATED DOCUMENTS | 3RD ANGLE PROJECTION  | THIS DRAWING IS CONFIDENTIAL AND THE PROPERTY OF TURCK INC. USE OF THIS DOCUMENT WITHOUT WRITTEN PERMISSION IS PROHIBITED. | <p>3000 CAMPUS DRIVE<br/>MINNEAPOLIS, MN 55441<br/>1-800-544-7769<br/>(763) 553-7300<br/>(763) 553-0708 fax<br/>www.turck.us</p> |   |
| 1.                |   | DRFT RDS   | DATE 07/13/04  | DESCRIPTION<br>RKC 4.4T-*--RSC 4.4T/CS11298 |
| 2.                |   | APVD RT  | SCALE 1=1.0  |   |
| 3.                | ALL DIMENSIONS DISPLAYED ON THIS DRAWING ARE FOR REFERENCE ONLY | UNIT OF MEASUREMENT<br><b>MILLIMETER [ INCH ]</b>  |  | IDENTIFICATION NO.                          |
| 4.                |   | CONTACT TURCK FOR MORE INFORMATION   |  | REV<br>E                                    |
| MATERIAL          | SEE SPECIFICATIONS  | DO NOT SCALE THIS DRAWING  |  | FILE: 777014026                             |
| FINISH            | SEE SPECIFICATIONS  |  |  | SHEET 1 OF 1                                |

|     |                              |    |          |         |
|-----|------------------------------|----|----------|---------|
| E   | UPDATED M12 MALE CTA PER ECO | TV | 11/15/16 | 52506   |
| REV | DESCRIPTION                  | BY | DATE     | ECO NO. |



| SPECIFICATIONS                    |                                   |
|-----------------------------------|-----------------------------------|
| CONTACT CARRIER MATERIAL/COLOR    | NYLON OR TPU/YELLOW               |
| MOLDED HEAD MATERIAL/COLOR        | TPU/RED                           |
| CONTACT MATERIAL/PLATING          | BRASS/GOLD                        |
| COUPLING NUT MATERIAL/PLATING     | BRASS/NICKEL                      |
| RATED CURRENT [A]                 | 4.0 A                             |
| RATED VOLTAGE [V]                 | 250 VAC/300 VDC                   |
| OUTER CABLE JACKET MATERIAL/COLOR | PVC/RED                           |
| CONDUCTOR INSULATION MATERIAL     | PVC                               |
| NUMBER OF CONDUCTORS [AWG]        | 4x18 AWG                          |
| TEMPERATURE RANGE                 | -40°C to +105°C (-40°F to +221°F) |
| PROTECTION CLASS                  | MEETS NEMA 1,3,4,6P AND IEC IP68  |



| CABLE LENGTH | TOLERANCE *   |
|--------------|---|
| ALL LENGTHS  | + 4% (OR 50mm) OF LENGTH<br>- 0% (OR 0mm) OF LENGTH<br>WHICHEVER IS GREATER |
| STRIP LENGTH | TOLERANCE *   |
| 0-7mm        | ±0.5mm  |
| 8-29mm       | ±1.0mm  |
| 30-49mm      | ±2.0mm  |
| 50-69mm      | ±3.0mm  |
| 70-100mm     | ±4.0mm  |
| OVER 100mm   | ±5.0mm  |

\* UNLESS OTHERWISE SPECIFIED

NOTES:

1. "\*" INDICATES CABLE LENGTH IN METERS. CONTACT TURCK TO ORDER SPECIFIC LENGTHS.

2. "/CS11298" DESIGNATES RED, PVC CABLE (10150896), 4x18 AWG, WITH RED MOLDED PLUG BODIES.

SOURCE DRAWING - FOR REFERENCE ONLY

|   |   |  |                     |  |
|---|---|--|---------------------|--|
| RELATED DOCUMENTS<br>1.<br>2.<br>3.<br>4. | 3RD ANGLE PROJECTION<br>  | THIS DRAWING IS CONFIDENTIAL AND THE PROPERTY OF TURCK INC. USE OF THIS DOCUMENT WITHOUT WRITTEN PERMISSION IS PROHIBITED. |                     | <p>3000 CAMPUS DRIVE<br/>MINNEAPOLIS, MN 55441<br/>1-800-544-7769<br/>(763) 553-7300<br/>(763) 553-0708 fax<br/>www.turck.us</p> |
|   |   | MATERIAL<br>SEE SPECIFICATIONS   | DRFT RDS<br>APVD RT |  |
| FINISH<br>SEE SPECIFICATIONS              | ALL DIMENSIONS DISPLAYED ON THIS DRAWING ARE FOR REFERENCE ONLY<br><br>CONTACT TURCK FOR MORE INFORMATION | UNIT OF MEASUREMENT<br><b>MILLIMETER [ INCH ]</b>  |                     | IDENTIFICATION NO.<br>REV<br>E   |
| DO NOT SCALE THIS DRAWING                 |   | FILE: 777014026  |                     | SHEET 1 OF 1   |

|     |                              |    |          |         |
|-----|------------------------------|----|----------|---------|
| E   | UPDATED M12 MALE CTA PER ECO | TV | 11/15/16 | 52506   |
| REV | DESCRIPTION                  | BY | DATE     | ECO NO. |