

Conduit



Stainless



Description

Robroy Stainless Rigid Conduit is designed to provide protection for wiring and cable in electrical systems and withstand harsh corrosive environments. Conduit is available in 304 or 316 and polished to a bright finish allowing for a surface that requires minimal cleaning. Each 10' length of conduit is threaded at both ends and supplied with one coupling. Conduit is manufactured using center aligned technology for adherence to tighter tolerances for a better system installation. Couplings are specifically designed with longer throats and chamfered connection points to eliminate exposed threads and the build up of dirt and contaminants that would otherwise occur at the threads which also minimizes risk of corrosion.

Standards

- cULus Listed
- UL 6A
- CSA C22.2 No. 45.2-08
- UL File Number: E98405

Catalog No.	Description	Weight Per Foot (lbs.)	Outside Diameter (in.)	Length (ft.)
RSCND304-050	Conduit 1/2 Inch 304	0.87	0.84	10
RSCND304-075	Conduit 3/4 Inch 304	1.15	1.05	10
RSCND304-100	Conduit 1 Inch 304	1.71	1.32	10
RSCND304-125	Conduit 1-1/4 Inch 304	2.32	1.66	10
RSCND304-150	Conduit 1-1/2 Inch 304	2.77	1.90	10
RSCND304-200	Conduit 2 Inch 304	3.73	2.38	10
RSCND304-250	Conduit 2-1/2 Inch 304	5.91	2.88	10
RSCND304-300	Conduit 3 Inch 304	7.73	3.50	10
RSCND304-400	Conduit 4 Inch 304	11.01	4.50	10
RSCND316-050	Conduit 1/2 Inch 316	0.87	0.84	10
RSCND316-075	Conduit 3/4 Inch 316	1.15	1.05	10
RSCND316-100	Conduit 1 Inch 316	1.71	1.32	10
RSCND316-125	Conduit 1-1/4 Inch 316	2.32	1.66	10
RSCND316-150	Conduit 1-1/2 Inch 316	2.77	1.90	10
RSCND316-200	Conduit 2 Inch 316	3.73	2.38	10
RSCND316-250	Conduit 2-1/2 Inch 316	5.91	2.88	10
RSCND316-300	Conduit 3 Inch 316	7.73	3.50	10
RSCND316-400	Conduit 4 Inch 316	11.01	4.50	10