

Close Nipples



Stainless



Description

Robroy Stainless Steel nipples are designed to withstand harsh corrosive environments. Nipples are available in 304 or 316 and are used to extend conduit systems and can be connected to boxes, enclosures, fittings, and other lengths of conduit.

Standards

- cULus Listed
- UL 6A
- CSA C22.2 No. 45.2-08
- UL File Number: E98405

Part	Description	Weight Each (lbs.)	Outside Diameter (in.)	Length (in.)
RSNIP304-050	Nipple 1/2 Inch 304 Close	0.08	0.84	1.13
RSNIP304-075	Nipple 3/4 Inch 304 Close	0.13	1.05	1.38
RSNIP304-100	Nipple 1 Inch 304 Close	0.21	1.32	1.50
RSNIP304-125	Nipple 1-1/4 Inch 304 Close	0.31	1.66	1.63
RSNIP304-150	Nipple 1-1/2 Inch 304 Close	0.40	1.90	1.75
RSNIP304-200	Nipple 2 Inch 304 Close	0.62	2.38	2.00
RSNIP304-250	Nipple 2-1/2 Inch 304 Close	1.23	2.88	2.50
RSNIP304-300	Nipple 3 Inch 304 Close	1.69	3.50	2.63
RSNIP304-400	Nipple 4 Inch 304 Close	2.64	4.50	2.88
RSNIP316-050	Nipple 1/2 Inch 316 Close	0.08	0.84	1.13
RSNIP316-075	Nipple 3/4 Inch 316 Close	0.13	1.05	1.38
RSNIP316-100	Nipple 1 Inch 316 Close	0.21	1.32	1.50
RSNIP316-125	Nipple 1-1/4 Inch 316 Close	0.31	1.66	1.63
RSNIP316-150	Nipple 1-1/2 Inch 316 Close	0.40	1.90	1.75
RSNIP316-200	Nipple 2 Inch 316 Close	0.62	2.38	2.00
RSNIP316-250	Nipple 2-1/2 Inch 316 Close	1.23	2.88	2.50
RSNIP316-300	Nipple 3 Inch 316 Close	1.69	3.50	2.63
RSNIP316-400	Nipple 4 Inch 316 Close	2.64	4.50	2.88