

# Eaton S10N04A83N

Catalog Number: S10N04A83N

Eaton General purpose encapsulated transformer, buck-boost general-purpose encapsulated transformer, EP, aluminum, NEMA 3R, 55, 60 Hz, single-phase, 120 V, 240 V, 12/24 V, NONE, 115 °C rise, 0.15 KVA, indoor-outdoor, 3B

## General specifications



Photo is representative

<b>Product Name</b>	<b>Catalog Number</b>
Eaton General purpose encapsulated transformer	S10N04A83N
	<b>UPC</b>
	786680383120

<b>Product Length/Depth</b>	<b>Product Height</b>
4 in	8.91 in

<b>Product Width</b>	<b>Product Weight</b>
4.11 in	8 lb

<b>Warranty</b>	<b>Certifications</b>
Eaton Selling Policy 25-000, one (1) year UL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	<b>Catalog Notes</b>
	Model N

## Physical Attributes

### Coil material

Aluminum

### Design

EP

### Enclosure

NEMA 3R

### Frame

55

### Tap size

None

### Type

Buck-Boost General-Purpose Encapsulated Transformer

### Wiring connection

3B

## Performance Ratings

### Frequency rating

60 Hz

### Phase

Single-phase

### Primary voltage

120 V, 240 V

### Secondary Voltage

12/24 V

### Temperature rise

115 °C rise

### Volt ampere rating

0.15 kVA

## Miscellaneous

### Weathershield

Indoor-Outdoor

## Resources

### Catalogs

Eaton's Volume 2—Commercial Distribution

### Specifications and datasheets

Eaton Specification Sheet - S10N04A83N



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia