

# Specifications

## Eaton S10N04P01P

Eaton General-Purpose Encapsulated Transformer, EP, Single-phase, PV: 120 X 240V, Taps: None, SV: 12/24V, 115°C, 1 kVA, Al windings, Frame: 67P, Indoor-Outdoor.



Photo is representative



### General specifications

<b>PRODUCT NAME</b>	Eaton General purpose encapsulated transformer
<b>CATALOG NUMBER</b>	S10N04P01P
<b>UPC</b>	786680072703
<b>PRODUCT LENGTH/DEPTH</b>	6.56 in
<b>PRODUCT HEIGHT</b>	13.03 in
<b>PRODUCT WIDTH</b>	5.53 in
<b>PRODUCT WEIGHT</b>	26 lb
<b>WARRANTY</b>	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
<b>CERTIFICATIONS</b>	UL Listed



Powering Business Worldwide

## Physical Attributes

COIL MATERIAL	Aluminum
DESIGN	EP
ENCLOSURE	NEMA 3R
FRAME	67P
TAP SIZE	None
TYPE	General-Purpose Encapsulated Transformer
WIRING CONNECTION	3B

## Miscellaneous

WEATHERSHIELD	Indoor-Outdoor
---------------	----------------

## Performance Ratings

FREQUENCY RATING	60 Hz
KVA RATING	1 kVA
PHASE	Single-phase
PRIMARY VOLTAGE	120 V, 240 V
SECONDARY VOLTAGE	12/24 V
TEMPERATURE RISE	115 °C rise
VOLT AMPERE RATING	1 kVA

## Resources

CATALOGS	<a href="#">Commercial Distribution, Transformers, Volume 2, Tab 2</a>
SPECIFICATIONS AND DATASHEETS	<a href="#">Eaton Specification Sheet - S10N04P01P</a>

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark. Follow us on social media to get the latest product and support information.

All other trademarks are property of their respective owners.



# Specifications

## Eaton S10N04P01P

Eaton General-Purpose Encapsulated Transformer, EP, Single-phase, PV: 120 X 240V, Taps: None, SV: 12/24V, 115°C, 1 kVA, Al windings, Frame: 67P, Indoor-Outdoor.



Photo is representative



### General specifications

<b>PRODUCT NAME</b>	Eaton General purpose encapsulated transformer
<b>CATALOG NUMBER</b>	S10N04P01P
<b>UPC</b>	786680072703
<b>PRODUCT LENGTH/DEPTH</b>	6.56 in
<b>PRODUCT HEIGHT</b>	13.03 in
<b>PRODUCT WIDTH</b>	5.53 in
<b>PRODUCT WEIGHT</b>	26 lb
<b>WARRANTY</b>	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
<b>CERTIFICATIONS</b>	UL Listed



Powering Business Worldwide

## Physical Attributes

COIL MATERIAL	Aluminum
DESIGN	EP
ENCLOSURE	NEMA 3R
FRAME	67P
TAP SIZE	None
TYPE	General-Purpose Encapsulated Transformer
WIRING CONNECTION	3B

## Miscellaneous

WEATHERSHIELD	Indoor-Outdoor
---------------	----------------

## Performance Ratings

FREQUENCY RATING	60 Hz
KVA RATING	1 kVA
PHASE	Single-phase
PRIMARY VOLTAGE	120 V, 240 V
SECONDARY VOLTAGE	12/24 V
TEMPERATURE RISE	115 °C rise
VOLT AMPERE RATING	1 kVA

## Resources

CATALOGS	<a href="#">Commercial Distribution, Transformers, Volume 2, Tab 2</a>
SPECIFICATIONS AND DATASHEETS	<a href="#">Eaton Specification Sheet - S10N04P01P</a>

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark. Follow us on social media to get the latest product and support information.

All other trademarks are property of their respective owners.

