

Eaton S10N04P51P

Catalog Number: S10N04P51P

Eaton General-Purpose Encapsulated Transformer, EP, Single-phase, PV: 120 X 240V, Taps: None, SV: 12/24V, 115°C, .50 kVA, Al windings, Frame: 57P, Indoor-Outdoor.

General specifications



Photo is representative

Product Name	Catalog Number
Eaton General purpose encapsulated transformer	S10N04P51P
	UPC
	786680073588

Product Length/Depth	Product Height
5.18 in	9.34 in

Product Width	Product Weight
4.45 in	15 lb

Warranty	Certifications
Eaton Selling Policy 25-000, one (1) year UL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	

Physical Attributes

Coil material

Aluminum

Design

EP

Enclosure

NEMA 3R

Frame

57P

Tap size

None

Type

General-Purpose Encapsulated Transformer

Wiring connection

509A

Performance Ratings

Frequency rating

60 Hz

Kva Rating

0.50 kVA

Phase

Single-phase

Primary voltage

120 V, 240 V

Secondary Voltage

12/24 V

Temperature rise

115 °C rise

Volt ampere rating

0.5 kVA

Miscellaneous

Weathershield

Indoor-Outdoor

Resources

Catalogs

Eaton's Volume 2—Commercial Distribution

Specifications and datasheets

Eaton Specification Sheet - S10N04P51P



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia