

# Eaton S10N06P02P

Catalog Number: S10N06P02P

Eaton General purpose encapsulated transformer, EP, aluminum, NEMA 3R, 68P, 60 Hz, single-phase, 120 V, 240 V, 16/32 V, NONE, 115 °C rise, 2 KVA, indoor-outdoor, 3C

## General specifications



Photo is representative

<b>Product Name</b>	<b>Catalog Number</b>
Eaton General purpose encapsulated transformer	S10N06P02P
	UPC
	786680073618
<b>Product Length/Depth</b>	<b>Product Height</b>
6.32 in	13.78 in
<b>Product Width</b>	<b>Product Weight</b>
6 in	42 lb
<b>Warranty</b>	<b>Certifications</b>
Eaton Selling Policy 25-000, one (1) year UL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	

## Physical Attributes

### Coil material

Aluminum

### Design

EP

### Enclosure

NEMA 3R

### Frame

68P

### Tap size

None

### Type

General-Purpose Encapsulated Transformer

### Wiring connection

3C

## Performance Ratings

### Frequency rating

60 Hz

### Phase

Single-phase

### Primary voltage

120 V, 240 V

### Secondary Voltage

16/32 V

### Temperature rise

115 °C rise

### Volt ampere rating

2 kVA

## Miscellaneous

### Weathershield

Indoor-Outdoor

## Resources

### Specifications and datasheets

[Eaton Specification Sheet - S10N06P02P](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

# Eaton S10N06P02P

Catalog Number: S10N06P02P

Eaton General purpose encapsulated transformer, EP, aluminum, NEMA 3R, 68P, 60 Hz, single-phase, 120 V, 240 V, 16/32 V, NONE, 115 °C rise, 2 KVA, indoor-outdoor, 3C

## General specifications



Photo is representative

<b>Product Name</b>	<b>Catalog Number</b>
Eaton General purpose encapsulated transformer	S10N06P02P
	UPC
	786680073618
<b>Product Length/Depth</b>	<b>Product Height</b>
6.32 in	13.78 in
<b>Product Width</b>	<b>Product Weight</b>
6 in	42 lb
<b>Warranty</b>	<b>Certifications</b>
Eaton Selling Policy 25-000, one (1) year UL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	

## Physical Attributes

### Coil material

Aluminum

### Design

EP

### Enclosure

NEMA 3R

### Frame

68P

### Tap size

None

### Type

General-Purpose Encapsulated Transformer

### Wiring connection

3C

## Performance Ratings

### Frequency rating

60 Hz

### Phase

Single-phase

### Primary voltage

120 V, 240 V

### Secondary Voltage

16/32 V

### Temperature rise

115 °C rise

### Volt ampere rating

2 kVA

## Miscellaneous

### Weathershield

Indoor-Outdoor

## Resources

### Specifications and datasheets

[Eaton Specification Sheet - S10N06P02P](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://Eaton.com/socialmedia)