

Specifications



Photo is representative



Eaton S10N06P51P

Eaton General purpose encapsulated transformer, EP, aluminum, NEMA 3R, 57P, 60 Hz, single-phase, 120 V, 240 V, 16/32 V, NONE, 115 °C rise, 0.5 KVA, indoor-outdoor, 3C

General specifications

| | |
|-----------------------------|--|
| PRODUCT NAME | Eaton General purpose encapsulated transformer |
| CATALOG NUMBER | S10N06P51P |
| UPC | 786680073656 |
| PRODUCT LENGTH/DEPTH | 5.18 in |
| PRODUCT HEIGHT | 9.34 in |
| PRODUCT WIDTH | 4.45 in |
| PRODUCT WEIGHT | 15 lb |
| WARRANTY | Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first. |
| CERTIFICATIONS | UL Listed |



Powering Business Worldwide

Physical Attributes

| | |
|-------------------|--|
| COIL MATERIAL | Aluminum |
| DESIGN | EP |
| ENCLOSURE | NEMA 3R |
| FRAME | 57P |
| TAP SIZE | None |
| TYPE | General-Purpose Encapsulated Transformer |
| WIRING CONNECTION | 3C |

Miscellaneous

| | |
|---------------|----------------|
| WEATHERSHIELD | Indoor-Outdoor |
|---------------|----------------|

Performance Ratings

| | |
|--------------------|--------------|
| FREQUENCY RATING | 60 Hz |
| PHASE | Single-phase |
| PRIMARY VOLTAGE | 120 V, 240 V |
| SECONDARY VOLTAGE | 16/32 V |
| TEMPERATURE RISE | 115 °C rise |
| VOLT AMPERE RATING | 0.5 kVA |

Resources

| | |
|-------------------------------|---|
| CATALOGS | Commercial Distribution Transformers, Volume 2, Tab 2 |
| SPECIFICATIONS AND DATASHEETS | Eaton Specification Sheet - S10N06P51P |

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark. Follow us on social media to get the latest product and support information.

All other trademarks are property of their respective owners.

