



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



S11252 Wi-Fi 9.5W Led A19 RGB/Tunable Bulb

Satco

Catalog Number	S11252
Manufacturer	Satco
Description	9.5 Watt - A19 Led Lamp - RGB and Tunable White - Starfish lot - 120 Volts - 800 Lumens
Weight per unit	0.2300 (lbs/each)
Product Category	Lighting

Features

average life	25000
Base	Medium
beam angle	220
lumens	800
Material	Plastic; Aluminum
Shape	A19
Warranty	3 Year Limited - 3 hr per day

Material, Color, and Finish

color temperature	5000
Finish	white

Dimensions and Weight

Size	4.57
------	------

Descriptions

Description	WI-FI 9.5W LED A19 RGB/TUNABLE BULB
extra long description	SATCO S11252 9.5A19/LED/RGB/TW/SF
Long Description	9.5 Watt - A19 LED Lamp - RGB and Tunable White - Starfish IOT - 120 Volts - 800 Lumens
Product Type	9.5A19/Led/RGB/TW/SF
Special Features	Unavailable for sale in California ; Color temperature: Warm White to Natural Light ; Dimmable Only with Starfish App ; IoT enabled ; Actual watts: 9.5W ; Energy Star: Yes ; Warranty: 3 Year Limited - 3 hr per day ; Incandescent Equivalent: 60W ; Indoor/Outdoor: Indoor ; Material: Plastic and Aluminum ; Enclosed fixture rated: No ; Location rating: Damp ; Voice assistants supported: Siri - Alexa - Hey Google - SmartThings

Manufacturer Information

Brand	Satco
GTIN	00045923112522
Manufacturers Part Number	S11252
UPC	045923112522



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description LED A-LINE SHAPE LAMPS

Type Type A

Packaging

Carton 1

Weight 0.15

Weight Per each 0.23

Uses, Certifications, and Standards

Operating Temperature -20C (-4F) to a maximum of +45C (+113F)

standard cULus