



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



S11417 9.5W A19 Led 50K E26 120V Dimmable 4-PK

Satco

Catalog Number	S11417
Manufacturer	Satco
Description	9.5 Watt A19 Led - 5000K - Dimmable - Medium Base - 230 Degree Beam Angle - 4-Pack
Weight per unit	0.4200 (lbs/each)
Product Category	Lighting

Features

average life	15000
Base	Medium
beam angle	230
lumens	800
Material	Polycarbonate (PC); High Heat Conductive Plastic Housing
Shape	A19
Voltage Rating	120
Warranty	3 Year Limited
Wattage	10

Material, Color, and Finish

color temperature	5000
Finish	white

Descriptions

Description	9.5W A19 LED 50K E26 120V DIMMABLE 4-PK
extra long description	SATCO S11417 9.5A19/LED/850/120V/D/
Long Description	9.5 Watt A19 LED - 5000K - Dimmable - Medium Base - 230 Degree Beam Angle - 4-Pack
Product Type	9.5A19/Led/850/120V/D/4PK

Manufacturer Information

Brand	Satco
GTIN	00045923114175
Manufacturers Part Number	S11417
UPC	045923114175

Taxonomies, Classifications, and Categories

Category Description	LED A-LINE SHAPE LAMPS
Type	Type A

Packaging

Carton	1
Weight	0.08
Weight Per each	0.42



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Operating Temperature	-20C (-4F) to a maximum of +45C (+113F)
standard	cULus