



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



S11540 9.5W Led Squat Lamp 27K Gu24

Satco

Catalog Number	S11540
Manufacturer	Satco
Description	9.5 Watt Led Lamp 2700K GU24 Base 120 Volts
Weight per unit	0.1800 (lbs/each)
Product Category	Led Reflector Gu, MR R Shape L

Features

average life	25000
Base	GU24
beam angle	100
dimnable	No
lumens	800
Material	Plastic; Metal; Electronic Components
Shape	Type A
Voltage Rating	120
Warranty	5 Year Limited - 10 hr per day
Wattage	10

Material, Color, and Finish

color temperature	2700
-------------------	------

Dimensions and Weight

Diameter	2.75
Length	2.81

Descriptions

Description	9.5W LED SQUAT LAMP 27K GU24
extra long description	SATCO S11540 9.5W/SQUAT/LED/27K/GU2
Long Description	9.5 Watt LED Lamp 2700K GU24 Base 120 Volts
Product Type	9.5W/Squat/Led/27K/Gu24
Special Features	CEC Title 20: Compliant ; Lawful for sale in California ; Energy Star: No ; Enclosed Rated Lamp: No ; Incandescent Equivalent: 60W ; Lamp Appearance: Frosted ; Body Material: Plastic/Metal ; Shade Material: Plastic ; Operating Temperature: -25C (-13F) to a maximum of +45C (+113F) ; Safety Listing: cULus - Damp ; Country of Origin: China ; Warranty: 5 Year Limited

Manufacturer Information

Brand	Satco
GTIN	00045923115400
Manufacturers Part Number	S11540
UPC	045923115400



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	LED REFLECTOR GU, MR R SHAPE LAMPS
Type	LED Type A

Packaging

Carton	1
Package	6
Weight	0.14
Weight Per each	0.18

Uses, Certifications, and Standards

Operating Temperature	-25C (-13F) to a maximum of +45C (+113F)
-----------------------	--