



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



S11541 9.5W Led Squat Lamp 40K Gu24

Satco

Catalog Number	S11541
Manufacturer	Satco
Description	9.5 Watt Led Lamp 4000K GU24 Base 120 Volts
Weight per unit	0.1800 (lbs/each)
Product Category	Led Reflector Gu, MR R Shape L

Features

average life	25000
Base	GU24
beam angle	100
dimnable	No
lumens	800
Material	Plastic; Metal; Electronic Components
Shape	Type A
Voltage Rating	120
Warranty	5 Year Limited - 10 hr per day
Wattage	10

Material, Color, and Finish

color temperature	4000
-------------------	------

Dimensions and Weight

Diameter	2.75
Length	2.81

Descriptions

Description	9.5W LED SQUAT LAMP 40K GU24
extra long description	SATCO S11541 9.5W/SQUAT/LED/40K/GU2
Long Description	9.5 Watt LED Lamp 4000K GU24 Base 120 Volts
Product Type	9.5W/Squat/Led/40K/Gu24
Special Features	CEC Title 20: Compliant ; Lawful for sale in California ; Energy Star: No ; Enclosed Rated Lamp: No ; Incandescent Equivalent: 60W ; Lamp Appearance: Frosted ; Body Material: Plastic/Metal ; Shade Material: Plastic ; Operating Temperature: -25C (-13F) to a maximum of +45C (+113F) ; Safety Listing: cULus - Damp ; Country of Origin: China ; Warranty: 5 Year Limited

Manufacturer Information

Brand	Satco
GTIN	00045923015410
Manufacturers Part Number	S11541
UPC	045923015410



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description LED REFLECTOR GU, MR R SHAPE LAMPS

Type LED Type A

Packaging

Carton 1

Package 6

Weight 0.14

Weight Per each 0.18

Uses, Certifications, and Standards

Operating Temperature -25C (-13F) to a maximum of +45C (+113F)