



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## S12400 5A15/CL/Led/E26/927/120V

Satco

Catalog Number	S12400
Manufacturer	Satco
Description	5 Watt Led A15 Lamp - Clear Medium Base 2700K 90 Cri 120 Volts
Weight per unit	0.1000 (lbs/each)
Product Category	Lighting

### Features

average life	15000
Base	Medium
beam angle	320
lumens	450
Material	Glass; Aluminum
Shape	A15
Warranty	3 Year Limited

### Material, Color, and Finish

color temperature	2700
Finish	Clear

### Dimensions and Weight

Size	3.39
------	------

### Descriptions

Description	5A15/CL/LED/E26/927/120V
extra long description	SATCO S12400 5A15/CL/LED/E26/927/12
Long Description	5 Watt LED A15 Lamp - Clear Medium Base 2700K 90 CRI 120 Volts
Product Type	5A15/CL/Led/E26/927/120V
Special Features	Lawful for sale in California ; Dimmable: Yes - Dimmable ; Color temperature: Warm White ; Incandescent equivalent: 40W ; Material: Aluminum and Glass ; Location rating: Wet ; Enclosed fixture rated: Yes ; Style: Vintage ; Operating temperature: -20C (-4F) to a maximum of 45C ( 113F) ; Warranty: 3 Year Limited

### Manufacturer Information

Brand	Satco
GTIN	00045923124006
Manufacturers Part Number	S12400
UPC	045923124006



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description	LED A-LINE SHAPE LAMPS
Type	A15

## Packaging

Carton	1
Weight	0.05
Weight Per each	0.1

## Uses, Certifications, and Standards

Operating Temperature	-20C (-4F) to a maximum of +45C (+113F)
standard	cULus Listed