



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



S128V 16-14 Bare Locking Spade #8 Stud

Nsi Industries

Catalog Number	S128V
Manufacturer	Nsi Industries
Description	Spade Terminal, Vinyl Insulated, 12-8 Wire Range, #8 Stud Size, Electro Tin Plated Copper With Brazed Seam, CULus Listed. Provides Safe and Reliable Connection Because It Cannot Be Disconnected Unless The Screw Is Completely Removed, Measures 0.812 Long By 0.375 Wide.
Weight per unit	0.2040 (lbs/each)
Product Category	Tools & Testers

Features

Material	Vinyl Insulation
Number of Terminals	1
Terminal Size	# 8
Voltage Rating	300 V
Wire Size	12-10 AWG

Material, Color, and Finish

Color	Yellow
-------	--------

Descriptions

Description	16-14 BARE LOCKING SPADE #8 STUD
extra long description	NSI S12-8V 16-14 Bare Locking Spade
Features	Spade terminal, vinyl insulated, 12-8 wire range, #8 stud size, electro tin plated copper with brazed seam, cULus listed. Provides safe and reliable connection because it cannot be disconnected unless the screw is completely removed, measures 0.812 long by 0.375 wide.
Long Description	Spade terminal, vinyl insulated, 12-8 wire range, #8 stud size, electro tin plated copper with brazed seam, cULus listed. Provides safe and reliable connection because it cannot be disconnected unless the screw is completely removed, measures 0.812 long by 0.375 wide.
Product Type	16-14 Bare Locking Spade # 10 Stud
Special Features	Vinyl Insulated Spade Terminal 12-10 AWG - 50 Pack

Manufacturer Information

Brand	NSi
GTIN	00662381062925
Manufacturers Part Number	S12-8V
UPC	662381062925



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	TERMINALS
Type	Vinyl Insulated Spade Terminal

Packaging

Carton	1
Package	50
Weight Per each	0.204

Uses, Certifications, and Standards

Application	Wire Termination
environmental conditions	75 C
standard	cULus